

Cutting head, right-hand, System / insert size: QC/09



Order data

Order number	260008 QC/09
GTIN	4251414902411
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: SCLCR/L 09

suitable indexable insert: CC.. 09T3..

suitable base body: 264900 – 264908

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre-line offset: 13 mm

Overall length: 20 mm

Technical description

Insert size	09 mm
suitable indexable insert	CC.. 09T3..
Overall length	20 mm

Insert screw	269023 2
System	QC
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Centre-line offset	13 mm
suitable base body	264900 – 264908
ISO code indexable cutting head	SCLCR/L 09
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Clamping screw	269407
Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500