

## Garant

**Solid carbide extension for screw-in milling cutters  $\varnothing d = 25$  mm, Thread M  $\times$  L: M12X216**



### Order data

Order number	301366 M12X216
GTIN	4045197770912
Item class	31Z

### Description

**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

### Technical description

Overall length $L_{tot}$	216 mm
Thread M	M12
Bore $\varnothing D_1$	12.5 mm
External $\varnothing D$	23 mm
Shank $\varnothing d$	25 mm
Reach $L_1$	160 mm
Adapter	$\varnothing d = 25$ mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

