



Manual vice for drilling machines, Jaw width A: 80mm



Order data

Order number	365045 80
GTIN	4045197771018
Item class	32D

Description

Version:

- **Sturdy and handy design.**
- **Jaws through hardened and ground.**
- **Consistent overall length (the spindle retracts into the handle)**
- **Universal fastening capability due to long holes.**
- **Movable jaw with guides at the sides.**
- **Fixed jaw with three vertical prismatic and one horizontal prismatic section.**

Application:

For clamping components on drilling machines.

Material:

Cast iron body.

Accuracy:

Within **0.20 mm.**

Technical description

Jaw height C	30 mm
Overall height c	64 mm
Weight	4 kg
Clamping range b	65 mm
Base body length a	233 mm

Jaw width A	80 mm
Type of product	Drilling machine vice

Accessories

Pair of spare jaws (2 pieces) for drilling machine manual vices for type 80	365046 80
---	-----------