

**Digital caliper ABS, Measuring range: 150HmMm****Order data**

Order number	412821 150HM
GTIN	4045197770240
Item class	42A

Description**Version:**

Large high-contrast digital display. The measuring faces are precision-lapped. Digital caliper with **absolute scale**, no zeroing required. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

- **Very high accuracy due to the glass scale.**
- **The electronics are decoupled from the casing and incorporated directly in the sliding part. The gauging force is transmitted directly to the measurement jaws. This reduces the liability of the caliper to errors and increases the working life.**
- **With sturdy metal body.**

With **carbide measuring faces** on jaws and tips.

Supplied with:

Supplied with battery No. 081560 size CR2032.

Technical description

Reversible reading	mm / inch
Measuring range	0 - 150 mm
Calibration	A1
Material of the housing	Metal
Jaw length	40 mm
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3

Auto switch-off	yes
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measurement face	Carbide
Depth gauge available	yes
Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Screw for depth gauge holder	412230
Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236