

**HOLEX****Digital caliper ABS, Measuring range: 300mm****Order data**

Order number	412821 300
GTIN	4045197770264
Item class	42A

**Description****Version:**

Large high-contrast digital display. The measuring faces are precision-lapped. Digital caliper with **absolute scale**, no zeroing required. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

- **Very high accuracy due to the glass scale.**
- **The electronics are decoupled from the casing and incorporated directly in the sliding part. The gauging force is transmitted directly to the measurement jaws. This reduces the liability of the caliper to errors and increases the working life.**
- **With sturdy metal body.**

**Supplied with:**

Including battery No. 081560 size CR2032.

**Technical description**

Reversible reading	mm / inch
Auto switch-off	yes
Depth gauge available	yes
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Jaw length	60 mm

Measuring range	0 - 300 mm
Calibration	A1
Material of the housing	Metal
Measured value saving	Once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.04$ mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

## Accessories

Screw for depth gauge holder	412230
Button cell / special battery Battery type CR2032	081560 CR2032
Plastic case Type MS300	412470 MS300
Screw for depth gauge holder	412236