



Digital caliper ABS with rod type depth gauge, Måleområde: 150



Order data

Order number	412818 150
GTIN	4045197770271
Item class	42A

Description

Version:

Large high-contrast digital display. The measuring faces are precision-lapped. Digital caliper with **absolute scale**, no zeroing required. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

- **Very high accuracy due to the glass scale.**
- **The electronics are decoupled from the casing and incorporated directly in the sliding part. The gauging force is transmitted directly to the measurement jaws. This reduces the liability of the caliper to errors and increases the working life.**
- **With sturdy metal body.**

Supplied with:

Supplied with battery No. 081560 size CR2032.

Packaging: sturdy box

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: \varnothing 1.6

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 inch

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Standard	DIN 862
----------	---------

Reversible reading	mm / inch
Measuring range	0 - 150 mm
Auto switch-off	yes
Error limit	0.03 mm
Depth gauge	Ø 1.6
Scale divisions	0.01 mm
Scale divisions	0.0005 inch
Calibration	A1
Jaw length	40 mm
Depth gauge available	yes
Measured value saving	Once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Vernier caliper standard

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Accessories

Plastic case Type MS150	412470 MS150
Button cell / special battery Battery type CR2032	081560 CR2032

Plastic case Type MS150	412468 MS150
Depth gauge holder	412230