




Digital depth gauge, Measuring range: 300mm



Order data

Order number	418742 300
GTIN	4045197771209
Item class	42A

Description

Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Extension base No. 418744.

Technical description

Scale divisions	0.01 mm
Reversible reading	0.0005 in
Bridge length	100 mm
Reversible reading	0.01 mm
Calibration	A1
Cross-section measuring beam	16×4 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement deviation E MPE	± 0.04 mm
Standard	ISO 13385

Reversible reading	mm / Inch
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D2	497100 D2
Button cell / special battery Battery type CR2032	081560 CR2032
Multi-receiver / USB keyboard interface Type	498975
Connecting cable Type D1	497080 D1
Connecting cable Type USB2	497080 USB2
Connecting cable with data switch Type USB2	497100 USB2
Screw for depth gauge holder	412230
Transmitter Type S1	498966 S1
Connecting cable with data switch Type D1	497100 D1
Connecting cable Type D2	497080 D2