

**Flat magnet with bore, Neodymium, Ø: 10mm****Order data**

Order number	085932 10
GTIN	2050001839480
Item class	08Q

**Description****Version:**

- **Temperature-resistant up to maximum 80 °C.**
- **Galvanised surface, magnetic core made of neodymium.**
- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**

**Application:**

For clamping, assembling, incorporation by screw fastening.

**Technical description**

Ø	10 mm
Height	4.5 mm
maximum temperature resistance	80 °C
Nominal clamping force	13 N
Bore Ø	3 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet