

**Garant**
**Clamp toolholder, right-hand, Shank / insert size: 32/19mm**

**Order data**

Order number	250016 32/19
GTIN	4045197771964
Item class	21T

**Technical description**

Insert size	19 mm
Shim	259031 36
ISO code toolholder	DCLNR/L 3232P19
suitable indexable insert	CN.. 1906..
Head length L <sub>1</sub>	40 mm
Shank size	32 mm
Clamp, screw, spring	259035 7
Overall length L	170 mm
Shim screw	259025 12
Functional width L <sub>4</sub>	40 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw 10 pieces Type 2	259026 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Shim Type 36	259031 36
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500