

**Garant**
**Clamp toolholder, left-hand, Shank / insert size: 32/16mm**

**Order data**

Order number	250017 32/16
GTIN	4045197771988
Item class	21T

**Technical description**

Shank size	32 mm
Shim	259031 35
suitable indexable insert	CN.. 1606..
Clamp, screw, spring	259035 6
Overall length L	170 mm
Shim screw	259025 11
Head length L <sub>1</sub>	40 mm
Functional width L <sub>4</sub>	40 mm
ISO code toolholder	DCLNR/L 3232P16
Insert size	16 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Shim screw Type 11	259025 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Shim Type 35	259031 35
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600