

Garant**Lever lock toolholder, right-hand, Shank / insert size: 25/16mm****Order data**

Order number	250020 25/16
GTIN	4045197772107
Item class	21T

Technical description

Shim pins pack	259044 6
Shim punches pack	259047 4
Lever	259015 12
Overall length L	150 mm
ISO code toolholder	PCBNR/L 2525M16
Insert size	16 mm
Head length L ₁	29 mm
Shank size	25 mm
Shim	259031 35
suitable indexable insert	CN.. 1606..
Functional width L ₄	22 mm
Lever screw	259018 11
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Lever screw Type 11	259018 11
Shim punches set 10 pieces Type 4	259047 4