

Garant**Lever lock toolholder, right-hand, Shank / insert size: 32/16mm****Order data**

Order number	250020 32/16
GTIN	4045197772114
Item class	21T

Technical description

ISO code toolholder	PCBNR/L 3232P16
suitable indexable insert	CN.. 1606..
Lever	259015 12
Shim pins pack	259044 6
Shim punches pack	259047 4
Functional width L ₄	27 mm
Shank size	32 mm
Insert size	16 mm
Overall length L	170 mm
Lever screw	259018 11
Head length L ₁	35 mm
Shim	259031 35
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Shim punches set 10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6