

Garant
Lever lock toolholder, right-hand, Shank / insert size: 32/19mm

Order data

Order number	250020 32/19
GTIN	4045197772121
Item class	21T

Technical description

ISO code toolholder	PCBNR/L 3232P19
Head length L ₁	35 mm
Insert size	19 mm
Functional width L ₄	27 mm
Shank size	32 mm
Overall length L	170 mm
Shim pins pack	259044 7
Lever screw	259018 13
Lever	259015 13
suitable indexable insert	CN.. 1906..
Shim punches pack	259047 5
Shim	259031 36
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 7	259044 7
Shim Type 36	259031 36
Lever screw Type 13	259018 13
Lever Type 13	259015 13