

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 32/16mm****Order data**

Order number	250021 32/16
GTIN	4045197772145
Item class	21T

**Technical description**

suitable indexable insert	CN.. 1606..
Lever screw	259018 11
Insert size	16 mm
Shim	259031 35
Shim pins pack	259044 6
Head length L <sub>1</sub>	35 mm
Functional width L <sub>4</sub>	27 mm
ISO code toolholder	PCBNR/L 3232P16
Shim punches pack	259047 4
Lever	259015 12
Overall length L	170 mm
Shank size	32 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

### Accessories

Shim punches set 10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Lever Type 12	259015 12
Set of shim pins 10 pieces Type 6	259044 6
Shim Type 35	259031 35