

Garant**Lever lock toolholder, left-hand, Shank / insert size: 32/19mm****Order data**

| | |
|--------------|---------------|
| Order number | 250021 32/19 |
| GTIN | 4045197772152 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| Overall length L | 170 mm |
| Shank size | 32 mm |
| Lever screw | 259018 13 |
| Lever | 259015 13 |
| Insert size | 19 mm |
| Head length L ₁ | 35 mm |
| suitable indexable insert | CN.. 1906.. |
| Shim | 259031 36 |
| Shim punches pack | 259047 5 |
| Shim pins pack | 259044 7 |
| ISO code toolholder | PCBNR/L 3232P19 |
| Functional width L ₄ | 27 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 75 degrees |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|-----------------------------------|-----------|
| Lever Type 13 | 259015 13 |
| Set of shim pins 10 pieces Type 7 | 259044 7 |
| Lever screw Type 13 | 259018 13 |
| Shim Type 36 | 259031 36 |