

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 25/16mm****Order data**

Order number	250025 25/16
GTIN	4045197772190
Item class	21T

**Technical description**

Overall length L	150 mm
Head length L <sub>1</sub>	33 mm
Shim	259031 35
Functional width L <sub>4</sub>	32 mm
Lever screw	259018 11
Shim pins pack	259044 6
Lever	259015 12
Shank size	25 mm
ISO code toolholder	PCSNR/L 2525M16
Shim punches pack	259047 4
Insert size	16 mm
suitable indexable insert	CN.. 1606..
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	45 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 35	259031 35
Lever Type 12	259015 12
Shim punches set10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Set of shim pins10 pieces Type 6	259044 6