

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 50/19mm**


## Order data

Order number	250037 50/19
GTIN	4045197772336
Item class	21T

## Technical description

Clamping height $L_2$	48 mm
Insert size	19 mm
Lever	259015 13
Overall length L	350 mm
Shim punches pack	259047 5
Minimum pre-drill $\varnothing D_{min}$	63 mm
suitable indexable insert	CN.. 1906..
Shim pins pack	259044 7
ISO code toolholder	A50U PCLNR/L19
Centre offset $L_3$	35 mm
Shim	259031 36
Lever screw	259018 13
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	50 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 36	259031 36
Set of shim pins 10 pieces Type 7	259044 7
Lever screw Type 13	259018 13
Lever Type 13	259015 13
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500