

Garant**Screw-on toolholder, right-hand, Shank / insert size: 25/12mm****Order data**

Order number	260004 25/12
GTIN	4045197772541
Item class	21T

Technical description

Shank size	25 mm
Pack of insert screws	269028 16
Insert size	12 mm
Functional width L ₄	27 mm
ISO code toolholder	SCRCR/L 2525M12
Overall length L	150 mm
Shim	269005 6
Head length L ₁	20 mm
Shim screw	269013 5
suitable indexable insert	CC.. 1204..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 16	269028 16
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Shim Type 6	269005 6
Shim screw Type 5	269013 5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500