

Garant**Screw-on toolholder, left-hand, Shank / insert size: 12/09mm****Order data**

Order number	260005 12/09
GTIN	4045197772572
Item class	21T

Technical description

Functional width L ₄	13 mm
Shank size	12 mm
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 8
Overall length L	80 mm
Insert size	9 mm
ISO code toolholder	SCRCR/L 1212F09
Head length L ₁	15 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500