

**Garant****Screw-on toolholder, left-hand, Shank / insert size: 20/12mm****Order data**

Order number	260005 20/12
GTIN	4045197772619
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	22 mm
Shim	269005 6
Shim screw	269013 5
Insert size	12 mm
Head length L <sub>1</sub>	20 mm
Pack of insert screws	269028 16
suitable indexable insert	CC.. 1204..
Overall length L	125 mm
ISO code toolholder	SCRCR/L 2020K12
Shank size	20 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

### Accessories

Shim screw Type 5	269013 5
Shim Type 6	269005 6
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Set of insert screws Type 16	269028 16
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500