

Garant

Swivel work chair, synthetic leather, with glides, low



Order data

Order number	965035
GTIN	4045197772640
Item class	91Z

Description

Version:

Ergonomic swivel work chair with synchro-technology. The soft synthetic leather surface is easy-clean and can be washed down. With orange offset double seam. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Standard:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

Standard:

DIN 68877

Load capacity chair: 120 kg

Height adjustment range: 490 - 630 mm

Seat width: 470 mm

Seat depth: 450 mm

Backrest height: 600 mm
 Seat depth adjustment range: 40 mm
 Backrest adjustment range: 60 mm
 Colour of seat material: black

Technical description

Backrest height	600 mm
Synchro mechanism	yes
Seat depth	450 mm
Colour of seat material	black
Standard	DIN 68877
Support frame version	5-point star base
Roller version	Load-responsive castor braking for hard floors.
Backrest adjustment range	60 mm
Safe working load	120 kg
Seat width	470 mm
Material of base	Aluminium matt powder coated
Armrest pair can be adjusted	yes
Lumbar support	yes
Continuous contact backrest adjustment	yes
Type of height adjustment	Height adjustment lever
Height adjustment version	Gas pressure spring
Material of seat surface	Synthetic leather
Seat depth adjustment range	40 mm
Base version	Glides
Version	without castors
Load capacity chair	120 kg
Height adjustment range	490 - 630 mm
Type of product	Swivel work chair

Accessories

Glides (1 set = 5 pieces)

962518

Pair of multi-function arm rests for the GARANT swivel work chair

965047