

Garant**Swivel work chair, synthetic leather, with glides, low****Order data**

| | |
|--------------|---------------|
| Order number | 965035 |
| GTIN | 4045197772640 |
| Item class | 91Z |

Description**Version:**

Ergonomic swivel work chair with synchro-technology. The soft synthetic leather surface is easy-clean and can be washed down. With orange offset double seam. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Version of the advertising text:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

Standard:

DIN 68877

Technical description

| | |
|--|--|
| Backrest height | 600 mm |
| Synchro mechanism | yes |
| Seat depth | 450 mm |
| Colour of seat material | black |
| Standard | DIN 68877 |
| Support frame version | 5-point star base |
| Roller version | Load-responsive castor braking for hard floors. |
| Backrest adjustment range | 60 mm |
| Safe working load | 120 kg |
| Seat width | 470 mm |
| Material of base | Aluminium matt powder coated |
| Armrest pair can be adjusted | yes |
| Lumbar support | yes |
| Continuous contact backrest adjustment | yes |
| Type of height adjustment | Height adjustment lever |
| Height adjustment version | Gas pressure spring |
| Material of seat surface | Synthetic leather |
| Seat depth adjustment range | 40 mm |
| Base version | Glides |
| Version | without castors |
| Load capacity chair | 120 kg |
| Height adjustment range | 490 - 630 mm |
| Type of product | Swivel work chair |

Accessories

| | |
|--------------------------|--------|
| Glides(1 set = 5 pieces) | 962518 |
| | 965047 |

Pair of multi-function arm rests for the GARANT swivel
work chair Type
