

Garant**Swivel work chair, synthetic leather, with glides and footrest ring, high****Order data**

Order number	965036
GTIN	4045197772657
Item class	91Z

Description**Version:**

Ergonomic swivel work chair with synchro-technology. The soft synthetic leather surface is easy-clean and can be washed down. With orange offset double seam. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Standard:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

Standard:**DIN 68877**

Load capacity chair: 120 kg

Height adjustment range: 640 - 890 mm

Seat width: 470 mm

Seat depth: 450 mm

Backrest height: 600 mm
 Seat depth adjustment range: 40 mm
 Backrest adjustment range: 60 mm
 Colour of seat material: black

Technical description

Continuous contact backrest adjustment	yes
Armrest pair can be adjusted	yes
Standard	DIN 68877
Safe working load	120 kg
Synchro mechanism	yes
Backrest adjustment range	60 mm
Base version	Glides with footrest ring
Material of seat surface	Synthetic leather
Material of base	Aluminium matt powder coated
Seat width	470 mm
Seat depth	450 mm
Backrest height	600 mm
Support frame version	5-point star base
Lumbar support	yes
Type of height adjustment	Height adjustment lever
Seat depth adjustment range	40 mm
Roller version	Load-responsive castor braking for hard floors.
Colour of seat material	black
Height adjustment version	Gas pressure spring
Version	high seat height
Load capacity chair	120 kg
Height adjustment range	640 - 890 mm
Type of product	Swivel work chair

Accessories

Glides (1 set = 5 pieces)

962518

Pair of multi-function arm rests for the GARANT swivel
work chair

965047