

**Garant****Swivel work chair, synthetic leather, with glides and footrest ring, high****Order data**

|              |               |
|--------------|---------------|
| Order number | 965036        |
| GTIN         | 4045197772657 |
| Item class   | 91Z           |

**Description****Version:**

Ergonomic swivel work chair with synchro-technology. The soft synthetic leather surface is easy-clean and can be washed down. With orange offset double seam. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

**Version of the advertising text:**

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

**Standard:**

**DIN 68877**

**Technical description**

|  |   |
|--|---|
| Continuous contact backrest adjustment | yes   |
| Armrest pair can be adjusted           | yes   |
| Standard                               | DIN 68877                                       |
| Safe working load                      | 120 kg  |
| Synchro mechanism                      | yes   |
| Backrest adjustment range              | 60 mm   |
| Base version                           | Glides with footrest ring                       |
| Material of seat surface               | Synthetic leather                               |
| Material of base                       | Aluminium matt powder coated                    |
| Seat width                             | 470 mm  |
| Seat depth                             | 450 mm  |
| Backrest height                        | 600 mm  |
| Support frame version                  | 5-point star base                               |
| Lumbar support                         | yes   |
| Type of height adjustment              | Height adjustment lever                         |
| Seat depth adjustment range            | 40 mm   |
| Roller version                         | Load-responsive castor braking for hard floors. |
| Colour of seat material                | black   |
| Height adjustment version              | Gas pressure spring                             |
| Version                                | high seat height                                |
| Load capacity chair                    | 120 kg  |
| Height adjustment range                | 640 - 890 mm                                    |
| Type of product                        | Swivel work chair                               |

## Accessories

|                          |        |
|--------------------------|--------|
| Glides(1 set = 5 pieces) | 962518 |
|                          | 965047 |

Pair of multi-function arm rests for the GARANT swivel  
work chair Type

---