



Flexible diamond files, Grit: D181 μ m



Order data

Order number	529120 D181
GTIN	4007220004968
Item class	53B

Description

Version:

Very thin plastic backing, coated **on one side** with diamond abrasive grit. Height including grit 0.5 mm.

Application:

Ideal for fine abrasive work on concave and convex surfaces, or in narrow slots. **Very high flexibility**, maximum bending radius 15 mm.

Technical description

Grit	D181
Grit designation	coarse
Dimensions	14×165 mm
Grinding media	Diamond
Grinding medium code	D
Width	14 mm
Height	0.5 mm
Length	165 mm
maximum bending radius	15 mm
Type of product	Diamond file

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		