

**LESSMANN**<sup>®</sup>  
THE GERMAN BRUSH COMPANY**Tube brush micro-abrasive (SiC) 120 grit, Brush Ø D1: 32mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 574475 32     |
| GTIN         | 4017359208199 |
| Item class   | 57L           |

**Description****Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles.

**Strong silicon carbide** bristles (**SiC**) in **120 grit and 320 grit**, bristle Ø **0.60mm**, overall length 125mm.

**Application:**

**Abrasive nylon brushes** work at both the tips and the sides of the bristles. The continued exposure of new abrasive material ensures an **even abrasive effect**. For **deburring** (cross) bores, O-ring recesses, and for **cleaning** and **polishing** nozzles and small hydraulic bores.

**Technical description**

|                               |            |
|-------------------------------|------------|
| Brush Ø D <sub>1</sub>        | 32 mm      |
| Working length L <sub>3</sub> | 65 mm      |
| Shank Ø D <sub>s</sub>        | 5.7 mm     |
| Type of product               | Tube brush |