


**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Wheel brush with shank micro-abrasive SiC 120 grit, Brush Ø D1× bristle width L1: 30X6mm****Order data**

Order number	574440 30X6
GTIN	4017359111345
Item class	57L

**Description****Version:**

Abrasive nylon strands with silicon carbide, crimped into steel sleeve; **shank Ø 6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

Wet and dry fine rubbing down of aluminium, steel, stainless steel and plastics. Maximum operating temperature 80 °C.

**Technical description**

recommended speed	6000 min <sup>-1</sup>
maximum speed	15000 min <sup>-1</sup>
Length of brush section H <sub>1</sub>	6 mm
Brush Ø D <sub>1</sub>	30 mm
Shank Ø D <sub>s</sub>	6 mm
Grinding medium code	SiC
Type of product	Wheel brush

