

LESSMANN[®]
THE GERMAN BRUSH COMPANY**Wheel brush with shank Stainless steel wire 0.20 mm, Brush Ø D1× bristle width L1: 60X15mm****Order data**

Order number	574250 60X15
GTIN	4017359012505
Item class	57L

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Brush Ø D ₁	60 mm
maximum speed	15000 min ⁻¹
Length of brush section H ₁	17 mm
Bristle thickness	0.2 mm
Bristle width L ₁	15 mm
Shank Ø D _s	6 mm

Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush