

LESSMANN®
THE GERMAN BRUSH COMPANY

Wheel brush Right-left knotted, steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M: 125XM14mm



Order data

Order number	571205 125XM14
GTIN	4017359458693
Item class	57L

Description

Version:

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Right-left knotted for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards. With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

Number of twisted knots	20
maximum speed	12500 min ⁻¹
Brush Ø D ₁	125 mm
Length of brush section H ₁	29 mm

Bristle width L ₁	14 mm
Thread M	M14
Brush material	Steel wire
Type of product	Wheel brush