

LESSMANN®
THE GERMAN BRUSH COMPANY

Knotted end brush Stainless steel wire, Brush \varnothing D1× bristle thickness: 6X0,35mm



Order data

Order number	574900 6X0,35
GTIN	4017359208908
Item class	57L

Description

Version:

Smooth, knotted wire, crimped into steel ferrule, **shank \varnothing 6 mm**, even density, extremely wear-resistant.

Stainless wire quality 1.4401 (AISI 316). Carrier body with plastic sheathing for machining stainless steel.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. Single-plait end brush for pin-point work.

Technical description

Bristle thickness	0.35 mm
maximum speed	4500 min ⁻¹
Number of twisted knots	1
Length of brush section H ₁	25 mm
Shank \varnothing D _s	6 mm
Brush material	Stainless steel wire
Twisted knotting	left-hand plait
Type of product	End brush

