

LESSMANN®
THE GERMAN BRUSH COMPANY**Knotted end brush Steel wire, Brush Ø D1× bristle thickness: 6X0,35mm****Order data**

Order number	574800 6X0,35
GTIN	4017359208892
Item class	57L

Description**Version:**

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. One-knotted end brush for pin-point work.

Technical description

maximum speed	4500 min ⁻¹
Bristle thickness	0.35 mm
Brush Ø D ₁	6 mm
Length of brush section H ₁	25 mm
Number of twisted knots	1
Shank Ø D _s	6 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	End brush