

**LESSMANN**<sup>®</sup>  
THE GERMAN BRUSH COMPANY**Tube brush micro-abrasive (SiC) 1000 grit, Brush Ø D1: 5,5mm****Order data**

Order number	574476 5,5
GTIN	4017359290651
Item class	57L

**Description****Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles.

**Fine silicon carbide** bristles (**SiC**) in **1000grit**, brush Ø **0.25mm**, overall length 100mm.

**Application:**

**Abrasive nylon brushes** work at both the tips and the sides of the bristles. The continued exposure of new abrasive material ensures an **even abrasive effect**. For **deburring** (cross) bores, O-ring recesses, and for **cleaning** and **polishing** nozzles and small hydraulic bores.

**Technical description**

Brush Ø D <sub>1</sub>	5.5 mm
Working length L <sub>3</sub>	25 mm
Shank Ø D <sub>s</sub>	2.2 mm
Type of product	Tube brush