



## Adjustable spanners, side adjustment, overall length: 255 mm

### Order data

Order number	813940 255
GTIN	7314150191239
Item class	83F

### Description

#### Version:

With ergonomic handle of thermoplastic elastomer. Jaw position 15°. Precision hardened, treated for protection against rust, and chrome-plated. Measurement scale in mm on the left hand side.

#### Standard:

**ISO 6787; ASME B107.8M-2003; UNE 16532**

maximum width across flats: 35 mm

overall length: 10 inch

### Technical description

Manufacturing process	precision hardened, treated for protection against rust
Jaw position	15 degrees
Grips	yes
Surface	chrome-plated
Material	High-performance steel alloy
Reversible jaws	no
Ratchet function	no
Norm	UNE 16532
Norm	ISO 6787
Norm	ASME B107.8M-2003
non-sparking	no

Scaling	yes
Type of product	