



Adjustable spanners, side adjustment, overall length: 205 mm



Order data

Order number	813940 205
GTIN	7314150191222
Item class	83F

Description

Version:

With ergonomic handle of thermoplastic elastomer. Jaw position 15°. Precision hardened, treated for protection against rust, and chrome-plated. Measurement scale in mm on the left hand side.

Standard:

ISO 6787; ASME B107.8M-2003; UNE 16532

maximum width across flats: 27 mm

overall length: 8 inch

Technical description

overall length	205 mm
overall length	8 inch
maximum width across flats	27 mm
Weight	300 g
Norm	UNE 16532
Norm	ISO 6787
Norm	ASME B107.8M-2003
Jaw position	15 degrees
Manufacturing process	precision hardened, treated for protection against rust

Material	High-performance steel alloy
Surface	chrome-plated
non-sparking	no
Reversible jaws	no
Scaling	yes
Ratchet function	no
Grips	yes