



Knurl forming tool universal, Shank size: 20mm



Order data

Order number	290010 20
GTIN	4030741658020
Item class	29H

Description

Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Modular design: Can be used as a right-hand or left-hand version. Click-Pin: For quick and easy changing of the knurl.

Technical description

Shank height	20 mm
Working range	10 - 110 mm
for knurl $\varnothing d_1$	20 mm
for knurl bore $\varnothing d_2$	6 mm
Roller pin	299910 4
Shank width	20 mm
for knurl width w	8 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 2×BL
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR

for knurl profile	RGE30° BL/BR30°
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

Accessories

Carbide roller pinCarbide Type 4	299910 4
----------------------------------	----------