

Garant**T-nut with clamping screw, Slot width B / clamping thickness S: 12/40mm****Order data**

Order number	360024 12/40
GTIN	2050001853936
Item class	310

Description**Version:**

Socket-head screw with hexagon socket to DIN912, strength class 12.9. The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Technical description

Clamping screw length	45 mm
Thread M	M10
Slot width B	12 mm
Clamping thickness S	40 mm

Series	ZeroClamp
Type of product	Tee-nut