

Garant**T-nut with clamping screw, Slot width B / clamping thickness S: 16/50 mm****Order data**

Order number	360024 16/50
GTIN	2050001854001
Item class	310

Description**Version:**

Socket-head screw with hexagon socket to DIN912, strength class 12.9.

Thread M: M14

Clamping screw length: 60 mm

Technical description

Thread M	M14
Clamping screw length	60 mm
Slot width B	16 mm
Clamping thickness S	50 mm
Series	ZeroClamp
Type of product	Accessories for zero-point clamping system

