

 steinel
Heat gun, Type: 351502

Order data

Order number	078321 351502
GTIN	4007841351502
Item class	07E

Description

Version:

Electronically controlled heat gun HG 2320 E.

- **Temperature adjusted digitally from 80 – 650°C using joystick**
- **Temperature displayed in 10°C increments via LCD display**
- **Air volume controlled in 2 stages from 150 – 500 l/min.**

Heat gun set HG 2320 EKF in a plastic case, consisting of:

- **Heat gun with stepless air flow control, four memory programmes, temperature and residual heat display, LOC function, single-hand operation.**
- **Reducer nozzle 9 mm, wide angle nozzle 50 mm, reflector nozzle, 100-piece shrink sleeve set.**

Application:

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

Technical description

Manufacturer's designation	HG 2320EKF
Air temperature	80 - 650 °C
Weight	960 g

Air flow volume	150 - 500 l/min
Version	Set
Power consumption	2300 W
Packaging	transport suitcase
Power supply	Mains operated
Type of product	Hot air pistol

Accessories

Heat gun accessory set 12 pieces Type 075569	078329 075569
Temperature scanner HG Scan PRO Type 007690	078325 007690
Temperature scanner HG Scan PRO Type 007553	078325 007553
Temperature scanner HL Scan Type 014919	078326 014919