

HOLEX**Heavy all-steel high-performance clamp with special jaw anvil, Jaw capacity: 500mm****Order data**

Order number	861320 500
GTIN	4045197775108
Item class	82C

Description**Version:**

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay. Spindle tempered and burnished with adjustable clamp handle.

Can tilt through 30°.

Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces. **Maximum clamping pressure up to approx. 22000 N.**

Technical description

Weight	6.6 kg
Cross section of the slide rail	40×20 mm

Throat	175 mm
Jaw capacity	500 mm
Type of product	Clamp

Accessories

Pressure plate Type GSV	861121 GSV
Pressure plate Type GSP	861121 GSP