

**HOLEX****Heavy all-steel high-performance clamp with special jaw anvil, Jaw capacity: 800mm****Order data**

Order number	861320 800
GTIN	4045197775139
Item class	82C

**Description****Version:**

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay. Spindle tempered and burnished with adjustable clamp handle.

Can tilt through 30°.

**Application:**

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces. **Maximum clamping pressure up to approx. 22000 N.**

**Technical description**

Throat	175 mm
Jaw capacity	800 mm

Cross section of the slide rail	40×20 mm
Weight	8.5 kg
Type of product	Clamp

---

## Accessories

Pressure plate Type GSP	861121 GSP
Pressure plate Type GSV	861121 GSV