

Garant**Grooving toolholder, right-hand, Shank size: 12mm****Order data**

Order number	273910 12
GTIN	4045197777263
Item class	21W

Description**Note:**

For **right-hand toolholders** use **right-hand inserts**, for **left-hand toolholders** use **left-hand inserts**.

Technical description

Shank size	12 mm
Free length	1.2 mm
Head length L ₁	21.4 mm
Functional width L ₄	16.2 mm
Insert screw	279815 13
Overall length L	100 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Boring bar

Accessories

Clamping screw Type 13	279815 13
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500