



Magnesium lever clamp, Jaw capacity: 200mm



Order data

Order number	860750 200
GTIN	4008158027241
Item class	83K

Description

Version:

Moving jaw and fixed jaw of **magnesium** (die-cast), **high strength and extremely light**. Beam of bright drawn steel, electro-galvanised. Clamping lever, movable jaw and locking pawl of **glass fibre reinforced plastic, unbreakable**. Fixed jaw with removable plastic cap with a cross Vee for clamping round parts underneath. Clamping lever with self-locking ratchet clamping mechanism. Opens by releasing the ratchet.

Application:

For **fast** and easy **clamping with medium clamping pressure**.

Technical description

Cross section of the slide rail	20x5 mm
Weight	0.32 kg
Jaw capacity	200 mm
Throat	80 mm
Type of product	Clamp

