

Garant
Stepped jaw movable, for type: 125

Order data

Order number	360468 125
GTIN	4045197777928
Item class	31F

Description
Application:

Accepts all high pressure jaws No. 362390 – 362600.

Material:

Hardened steel, ground surfaces.

Suitable for:

NC high pressure vices No. 360400; 360465; 360500; 360510; 361301.

Technical description

Height h_1	20 mm
Length l_1	40 mm
Jaw height h	39.5 mm
Jaw width b	125 mm
suitable for colour code	LC-GARANT
suitable for colour code	TC
suitable for colour code	HiPo
suitable for colour code	Duo

suitable for colour code	NC8
suitable for colour code	HOLEX NC
suitable for colour code	LC
suitable for colour code	Titan
suitable for colour code	Titan2/TitanSense
Jaw length l	70 mm
Type of product	Vice jaws