

Garant

eco grooving tool strengthened, right-hand, Blade height h₅ / groove width w: 26/3Lmm


Order data

Order number	273864 26/3L
GTIN	4045197778239
Item class	21W

Description
Version:

With eco cooling directly to the cutting edge and additional rake face cooling.

Suitable for:

Toolholder No. 273893; 273894; 274095; 274097 or VDI toolholder 319133. 319140 – 319141 size RR or LR.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.

Technical description

for maximum workpiece \varnothing	90 mm
Blade height h ₅	26 mm
Groove width w	3 mm
Height h ₁	21.4 mm
Series	Eco
Overall length L	109.5 mm
Application type	right-hand
Through-coolant	yes

axial grooving possible	no
Type of product	Parting-off tool