

Garant

eco grooving tool strengthened, left-hand, Blade height h₅ / groove width w: 26/3Lmm


Order data

Order number	273865 26/3L
GTIN	4045197778352
Item class	21W

Description
Version:

With eco cooling directly to the cutting edge and additional rake face cooling.

Suitable for:

Toolholder No. 273893; 273894; 274095; 274097 or VDI toolholder 319132. 319140 – 319141 size RL or LL.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149. Please order the assembly key No. 279920 separately. From 19.5 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

Technical description

Groove width w	3 mm
for maximum workpiece Ø	90 mm
Blade height h ₅	26 mm
Height h ₁	21.4 mm
Series	Eco
Overall length L	109.5 mm

Application type	left-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Parting-off tool