

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 20/11mm

Order data

Order number	261124 20/11
GTIN	4045197778376
Item class	21T

Technical description

Overall length L	180 mm
Pack of insert screws	269028 7
Neck width L ₄	11 mm
Head length L ₁	38 mm
ISO code toolholder	A20Q SVJBR/L11
Centre offset L ₃	2 mm
Minimum pre-drill Ø D _{min}	25 mm
Setting angle κ	142 degrees
Clamping height L ₂	19 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Shank Ø D _s	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500