

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/11 mm

Order data

Order number	261125 16/11
GTIN	4045197778390
Item class	21T

Technical description

Clamping height L_2	15 mm
suitable indexable insert	VB.. 1103..
Overall length L	150 mm
Neck width L_4	9.5 mm
Setting angle κ	142 degrees
ISO code toolholder	A16M SVJBR/L11
Pack of insert screws	269028 7
Head length L_1	31.4 mm
Centre offset L_3	2 mm
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500