

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 20/11 mm**

**Order data**

Order number	261125 20/11
GTIN	4045197778406
Item class	21T

**Technical description**

Neck width $L_4$	11 mm
Clamping height $L_2$	19 mm
Pack of insert screws	269028 7
Head length $L_1$	38 mm
Setting angle $\kappa$	142 degrees
suitable indexable insert	VB.. 1103..
Centre offset $L_3$	2 mm
ISO code toolholder	A20Q SVJBR/L11
Overall length $L$	180 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500