

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261125 25/16
GTIN	4045197778413
Item class	21T

Technical description

ISO code toolholder	A25R SVJBR/L16
Insert size	16 mm
Pack of insert screws	269028 8
Setting angle κ	142 degrees
Centre offset L_3	4.6 mm
Head length L_1	44 mm
Neck width L_4	16.5 mm
Overall length L	200 mm
suitable indexable insert	VB.. 1604..
Minimum pre-drill $\varnothing D_{\min}$	28 mm
Clamping height L_2	24 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 17

269028 17

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile
15IP

674252 15IP

Torque screwdriver with scale, to take interchangeable
blades maximum torque 500 cNm

659957 500