

**Garant**
**CNMG 160608, Grade: HB7010-1**


### Order data

Order number	250168 HB7010-1
GTIN	4045197779632
Item class	21G

### Description

CNMG 160608 HB7010-1 Grade: HB7010-1  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 8 mm  
 Feed  $f$ : 0.2 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 120 - 440 m/min

### Technical description

Corner radius	0.8 mm
Chip breaker	SM
Grade	HB7010-1
Cutting speed $v_c$ main application	120 - 440 m/min
Cutting conditions	continuous
Feed $f$	0.2 - 0.5 mm/rev.
Main application	P

Cutting depth $a_p$	0.5 - 8 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 160608
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning